

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz)	3500 ± 500
Operating Voltage (Vp-p/max)	150
Rated Voltage (Vp-p)	5.0 / 125
Current Consumption (mA/max)	4.0 / 47
Sound Pressure Level (dB/min)	90 @ 30cm / 105 @ 100cm
Capacitance (pF)	30,000 ±30% at 120Hz
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: Red / White / Black)
Lead Wire	2 Solder Pads
Weight (Grams)	31
Options	For other options contact factory

NO CIRCUITRY

Dimensions: (units: mm)

PS: Vp-p = 1/2duty, square wave

ROHS Compliant

