



Mallory Sonalert Products, Inc.

Part #:

SC648MD

Sales Outline Drawing

Revision:

D

Specifications:

MILITARY UNIT

Sound Level Category	Medium
Mode of Operation	Continuous
Voltage Rating	10 to 48 VDC
Frequency	2000 ± 500 Hz
Loudness @ 2 FT	66 to 79 dB(A) Typ.
Loudness @ Min Vdc	60 dB(A) min. @ 2 Feet and 10 Vdc
Loudness @ Max Vdc	75 dB(A) min. @ 2 Feet and 48 Vdc
Current Draw	5-20mA
Housing Material	6/6 Nylon, Color: Black
Storage Temperature	-65° to +85° C
Operating Temperature	-40° to +85° C
Panel Mounting	Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.
Knurled Nut	Used to attach part to panel. The max recommended torque is 10 in-lbs.
Weight (Typical)	1.6 oz (45g)
NEMA 3R,4X, & 12	Approved with use of ACC03.
Options	Please contact factory.

Dimensions: Inches (mm)

