

CHERRY GENTIX BT

Bluetooth® Mouse



Models may vary from the image shown

Bluetooth® mouse with multi-device function

The CHERRY GENTIX BT mouse is based on the GENTIX mouse, which has proven itself in practice millions of times over, and adds a convenient Bluetooth® function with multi-device capability.

Data is transmitted via a secure AES-128 encryption.

You can effortlessly connect it to various end devices, for example a PC, laptop, tablet, smartphone or even a smart TV by pressing the Bluetooth® button on the bottom of the wireless mouse. The mouse works with Windows, Android, macOS, iPadOS and Chrome OS.

The switchable, highly precise optical sensor offers enough precision and speed with 1000 / 2000 dpi to make every user – even those with very high requirements – happy. You can change conveniently between the two preset resolutions using the practical DPI switch. The scroll wheel will illuminate blue to indicate a change of resolution, mouse activation or low battery level.

You can navigate back and forth in your browser at lightning speed with the two additional thumb buttons of the wireless computer mouse. The free CHERRY KEYS software is available for the individual assignment of the mouse buttons.

The rubberized side panels are unchanged from the proven GENTIX mice. They provide a firm grip and feel pleasant in your hand. The shape tapers towards the back meaning that the mouse has perfect ergonomics - for both small and large hands.

Fans of wireless freedom can look forward to a battery life of up to one year (depending on usage). Simply store the CHERRY GENTIX BT in the included pouch for transport. The wireless mouse is ready to use in a flash and requires no additional software.

The most important advantages

- High-precision optical sensor
- Two-level adjustable resolution (1,000/2,000 dpi)
- Multi-device function for up to three end devices
- Perfect ergonomics for small and large hands
- 7 buttons and a scroll wheel
- Fits snugly in the hand
- Rubber-coated side sections for optimal grip
- Transmission via encrypted Bluetooth® 5.0 (AES-128)
- Transport pouch included

CHERRY GENTIX BT

Bluetooth® Mouse

Technical specifications

Weight (product)

approx. 75 g (Mouse)

approx. 96 g (Mouse incl. batteries)

Total weight (with packaging)

approx. 151 g

Storage temperature

-4 °F to 140 °F

Operating temperature

32 °F to 104 °F

Power consumption

5 mA

Product approvals

- CE
- FCC
- China RoHS
- UKCA
- Bluetooth® SIG licensing
- Windows hardware compatibility

System requirements

Bluetooth 4.0 or higher, Windows 11, Windows 10 /
macOS 11 or higher / iOS / Chrome OS / Android

Scope of delivery

- Mouse
- 2x AAA batteries
- Operating instructions
- Transport pouch

Product dimensions

approx. 112 x 70 x 35 mm

Packaging dimensions

140 x 78 x 45 mm

Mouse

- Scanning: optical
- Resolution: 1000 / 2000 dpi (adjustable)
- Number of buttons: 7
- Mouse wheel design: Scroll wheel with button function
- Design: Symmetrical
- Connection: Bluetooth®
- Product color: see table

Packaging unit

Number of products in outer package 10

Outer package on pallet: 114

Warranty:

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorised changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY GENTIX BT

Bluetooth® Mouse

Models

	Product name	Order number	Sales Region	EAN / UPC-Code	Color
1	CHERRY GENTIX BT	JW-7500-2	EU	4025112098857	black
2	CHERRY GENTIX BT	JW-7500US-2	US	840183606107 (UPC)	black
3	CHERRY GENTIX BT	JW-7501-2	Asia	4025112098864	black
4	CHERRY GENTIX BT	JW-7500-18	EU	4025112102851	agave green
5	CHERRY GENTIY BT	JW-7500US-18	US	840183606312 (UPC)	agave green
6	CHERRY GENTIX BT	JW-7501-18	Asia	4025112102868	agave green
7	CHERRY GENTIX BT	JW-7500-19	EU	4025112102882	cherry blossom
8	CHERRY GENTIX BT	JW-7500US-19	US	840183606329 (UPC)	cherry blossom
9	CHERRY GENTIX BT	JW-7501-19	Asia	4025112102899	cherry blossom
10	CHERRY GENTIX BT	JW-7500-20	EU	4025112102912	frosted silver
11	CHERRY GENTIX BT	JW-7500US-20	US	840183606336 (UPC)	frosted silver
12	CHERRY GENTIX BT	JW-7501-20	Asia	4025112102929	frosted silver

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.