

## Industrial Power Strip, 3-Outlet, 9 ft. (2.7 m) Cord, NEMA 5-15P Plug, Switch Guard

MODEL NUMBER: 3SP9



Durable all-metal industrial power strip distributes power to appliances, power tools, lights and other heavy-duty electrical equipment in industrial and commercial settings.

### Description

The 3SP9 3-Outlet Industrial Power Strip is the perfect power distribution solution for appliances, power tools, lighting and other electrical equipment in both industrial and commercial settings. Its rugged all-metal housing is designed for demanding environments, making it ideal for a factory floor, warehouse, server room or commercial space. Keyhole mounting tabs let you install the 3SP9 wherever convenient—on a wall, floor, workbench or under a counter.

Three NEMA 5-15R outlets are arranged in standard 1.75-inch center-to-center spacing for easy connection to equipment. A built-in unfiltered electrical pass through makes the 3SP9 ideal for distributing alternate waveform power from a UPS system or generator to connected equipment. The long nine-foot (2.7-meter) power cord with NEMA 5-15P plug lets the 3SP9 be mounted away from the power source for maximum convenience and flexibility.

A built-in 15A circuit breaker detects dangerous overloads that could damage valuable equipment and immediately shuts down the 3SP9. A transparent switch cover protects against accidental shutdowns. A lighted on/off switch confirms at a glance that the power strip is operating.

### Features

#### Perfect Worksite Power Distribution

- Ideal for powering appliances, power tools, lighting and other electrical equipment
- 3 NEMA 5-15R outlets with 1.75 in. center-to-center spacing
- 9-ft. (2.74 m) power cord with NEMA 5-15P plug
- Meets UL1363 (USA) and cUL (Canada) certifications

#### Premium Safety Features

- 15A resettable circuit breaker prevents dangerous overloads
- Transparent switch cover eliminates accidental shutdowns
- Lighted on/off switch confirms operation at a glance

#### Unfiltered Electrical Pass Through

- Distributes alternate waveform power from UPS system or generator to connected equipment

### Highlights

- 3 NEMA 5-15R outlets with 1.75 in. center-to-center spacing
- 15A resettable circuit breaker
- Lighted on/off switch with transparent safety cover
- Heavy-duty all-metal housing
- 9-ft. (2.74 m) power cord with NEMA 5-15P plug

### Package Includes

- 3SP9 3-Outlet Industrial Power Strip, 9 ft. (2.7 m) Cord
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

#### Heavy-Duty All-Metal Housing

- Designed for demanding environments, such as factories, warehouses, server rooms and commercial spaces
- 8.6 in. length for minimal footprint
- Keyhole mounting tabs for installation on a wall, floor, workbench or under a counter

## Specifications

| OVERVIEW                           |                                                                                         |
|------------------------------------|-----------------------------------------------------------------------------------------|
| UPC Code                           | 037332189653                                                                            |
| Product Type                       | Power Strip                                                                             |
| Charging Form Factor               | Strip                                                                                   |
| Device Compatibility               | Chromebook; Computer; Laptop; Monitor/HDTV; Phone; Projector; Tablet; Video Game System |
| INPUT                              |                                                                                         |
| Nominal Input Voltage(s) Supported | 120V AC                                                                                 |
| Recommended Electrical Service     | 15A 120V                                                                                |
| Input Cord Gauge Type              | 14 gauge; SJT                                                                           |
| Input Cord Gauge (AWG)             | 14 AWG                                                                                  |
| Voltage Compatibility (VAC)        | 120                                                                                     |
| Input Plug Type                    | NEMA 5-15P                                                                              |
| Input Cord Length (ft.)            | 9                                                                                       |
| Right-Angle Plug                   | No                                                                                      |
| Input Cord Length (m)              | 2.74                                                                                    |
| Integrated Cord Clip               | No                                                                                      |
| OUTPUT                             |                                                                                         |
| Frequency Compatibility            | 50 / 60 Hz                                                                              |
| Output (Watts)                     | 1800                                                                                    |
| Output Receptacles                 | (3) 5-15R                                                                               |
| Circuit Breaker (amps)             | 15                                                                                      |
| Overload Protection                | 15A circuit breaker                                                                     |
| Transformer Accommodation          | (1) Yes                                                                                 |
| Outlet Orientation                 | Single row of 3                                                                         |
| Right-Angle Outlets                | No                                                                                      |
| Outlet Spacing                     | 1.75 in.                                                                                |
| USER INTERFACE, ALERTS & CONTROLS  |                                                                                         |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                                   |                                                                             |
|---------------------------------------------------|-----------------------------------------------------------------------------|
| Switches                                          | Lighted 2 position switch controls power to all outlets                     |
| Locking Switch Cover                              | Transparent locking switch cover prevents accidental shutoff                |
| <b>PHYSICAL</b>                                   |                                                                             |
| Color                                             | Gray                                                                        |
| Material of Construction                          | Metal                                                                       |
| Power Cord Color                                  | Black                                                                       |
| Housing Color                                     | Blue; Gray                                                                  |
| Mounting Holes or Slots                           | Yes                                                                         |
| Slot or Hole Mount Measurement (Center to Center) | Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm |
| Receptacle Color                                  | Black                                                                       |
| Shipping Dimensions (hwd / in.)                   | 2.40 x 5.70 x 10.20                                                         |
| Shipping Dimensions (hwd / cm)                    | 6.10 x 14.48 x 25.91                                                        |
| Shipping Weight (lbs.)                            | 1.90                                                                        |
| Shipping Weight (kg)                              | 0.86                                                                        |
| Unit Dimensions (hwd / in.)                       | 1.500 x 8.750 x 2.500                                                       |
| Unit Dimensions (hwd / cm)                        | 3.81 x 22.2 x 6.35                                                          |
| Outlet Spacing                                    | 1.75 in.                                                                    |
| Mounting Details                                  | Includes flanges                                                            |
| <b>FEATURES &amp; SPECIFICATIONS</b>              |                                                                             |
| Antimicrobial                                     | No                                                                          |
| Built-In Circuit Breaker                          | Yes                                                                         |
| <b>STANDARDS &amp; COMPLIANCE</b>                 |                                                                             |
| Product Certifications                            | cUL Listed; UL 1363; UL Listed                                              |
| Product Compliance                                | RoHS                                                                        |
| <b>WARRANTY &amp; SUPPORT</b>                     |                                                                             |
| Product Warranty Period (Worldwide)               | Lifetime limited warranty                                                   |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.