

## Industrial Power Strip, 5-Outlet, 15 ft. (4.6 m) Cord, Switchless

MODEL NUMBER: 602-15



### Highlights

- 5 outlets
- 15-ft. (4.57 m) cord
- 8.6-in. overall length
- No switch
- All-metal housing

### Package Includes

- 602-15 Power Strip
- Warranty information
- Instruction manual

### Description

The 602-15 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes five NEMA 5-15R output receptacles with 1.188-inch center-to-center spacing, 15-foot (4.6-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Cabled, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 602-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, 15A resettable circuit breaker and attractive blue/gray color scheme.

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center outlet spacing
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15-amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

## Specifications

OVERVIEW	
UPC Code	037332113443
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120

Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(5) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 5
Right-Angle Outlets	No
Outlet Spacing	1.188 in.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	No power switch
<b>PHYSICAL</b>	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45
Outlets Measurement (Center to Center)	1.18 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.10 x 2.70 x 6.10
Shipping Dimensions (hwd / cm)	35.81 x 6.86 x 15.49
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
Unit Dimensions (hwd / in.)	1.500 x 8.750 x 2.500
Unit Dimensions (hwd / cm)	18.7 x 6.35 x 3.8
Outlet Spacing	1.188 in.
Mounting Details	Includes flanges



*Powering Business Worldwide*

TRIPP LITE  
SERIES

**FEATURES & SPECIFICATIONS**

Antimicrobial	No
Built-In Circuit Breaker	Yes

**STANDARDS & COMPLIANCE**

Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS

**WARRANTY & SUPPORT**

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.