

Toslink Digital Optical SPDIF Audio Cable, 2M (6.56 ft.)

MODEL NUMBER: A102-02M



Highlights

- Superior-grade optical fiber and precision polished optical terminations
- Best possible sound quality through digital fiber optic signals
- Immune to all forms of EMI/RFI

System Requirements

- Home Theater or Stereo equipment with Toslink capabilities

Package Includes

- 2-meter Toslink Digital Optical Audio Cable

Features

- Digital Optical Fiber offers the best in Audio clarity
- Precision polished optical termination minimizes loss for better high frequencies, and a more realistic stereo image
- Ultra flexible PVC jacket construction makes installation easy, even in hard to reach areas
- Immune to all Electromagnetic and Radio-Frequency interference
- Eliminates distortion caused by inductance, capacitance, and resistance found in copper cables

Specifications

OVERVIEW	
UPC Code	037332121912
Technology	Toslink/SPDIF; Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	TOSLINK (MALE)
Side B - Connector 1	TOSLINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6.6



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (m)	2.01
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.