

## Toslink Digital Optical SPDIF Audio Cable, 3M (9.84 ft.)

MODEL NUMBER: **A102-03M**



### Highlights

- Superior-grade optical fiber and precision polished optical terminations
- Best possible sound quality through digital fiber optic signals
- Immune to all forms of EMI/RFI

### System Requirements

- Home Theater or Stereo equipment with Toslink capabilities

### Package Includes

- 3-meter ( 10ft ) Toslink Digital Optical Audio Cable

### Features

- Digital Optical Fiber offers the best in Audio clarity
- Precision polished optical termination minimizes loss for better high frequencies, and a more realistic stereo image
- Ultra flexible PVC jacket construction makes installation easy, even in hard to reach areas
- Immune to all Electromagnetic and Radio-Frequency interference
- Eliminates distortion caused by inductance, capacitance, and resistance found in copper cables

## Specifications

OVERVIEW	
UPC Code	037332138781
Technology	Toslink/SPDIF; Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	TOSLINK (MALE)
Side B - Connector 1	TOSLINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	9.8



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Cable Length (m)	2.99
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.