

DVI/HDMI over IP Extender Transmitter over Cat5/Cat6, RS-232 Serial and IR Control, 1920 x 1080 (1080p), 328 ft. (100 m), TAA

MODEL NUMBER: B160-001-HDSI



Converts HDMI or DVI audio/video to an IP-based signal that is transmitted point-to-point to a receiver 328 ft. away via Cat5e/6 cable or through a dedicated Ethernet network switch.

Features

Distributes HDMI/DVI A/V, Serial and IR Control Signals over Cat5/6 Cabling Converts audio/video to an IP-based signal that is transmitted point-to-point to a display 328 ft. away Add low-cost network switches between transmitter and receiver to continue extending distance up to 328 ft. per switch HDMI output for connecting a local display

Create a Multi-In, Multi-Out Installation Using B160-Series Transmitters and Receivers Connect up to 64 transmitters and 255 receivers through multiple dedicated managed network switches IGMP-enabled switches allow centralized control over which sources show on which displays Video source can be sent to any analog or digital display, so you can mix and match technologies and use existing monitors

Enhanced Technical Features Supports video resolutions up to 1920 x 1080 (1080p) Uses H.264 video compression standard Transmits on 20–60 kHz IR frequency Extends IR control signals that control a source from a remote display Supports RS-232 serial baud rates up to 57600 Bps HDCP and 3D compatible when used with a DisplayPort or HDMI receiver

Plug-and-Play Functionality No software or drivers required Hardware included for mounting on wall, rack or pole Compatible with all B160-Series A/V over IP receivers

TAA-Compliant Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Compatible with B160-Series A/V over IP receivers
- Video source can be sent to any analog or digital display
- Supports video resolutions up to 1920 x 1080 (1080p) - Limited to maximum resolution of receiver
- HDMI output on transmitter for connecting local display
- Plug and play—no software or drivers required

Package Includes

- Transmitter unit
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Plug adapters for U.S., U.K., Europe and Australia
- IR-Out cable
- HDMI-to-DVI adapter cable
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332196644
Product Type	Transmitter
Technology	DVI; HDMI; IR; A/V over IP; Cat5/5e; Cat6



Powering Business Worldwide

TRIPP LITE
SERIES

VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	328
Max 1920 x 1080 (1080p) Range (ft)	328
Transmitter Video Input	HDMI or DVI w/ adapter
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Range Extension using other Tripp Lite product	328 ft.
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	network switch
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	328
Maximum Signal Range (m)	100
AUDIO	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	Stereo Audio
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.4
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No



Powering Business Worldwide

TRIPP LITE
SERIES

DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	5.8
CONNECTIONS	
Number of Ports	5
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE); RJ45 (FEMALE)
Side B - Connector 2	(2) 3.5MM (FEMALE)
Daisy-chainable / Cascadable	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45 Output (Green / Power, Orange / Signal), Channel Signal (Red), Power (Green)
PHYSICAL	
Color	Black
Material of Construction	Steel
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	2.10 x 6.30 x 10.10
Shipping Weight (lbs.)	2.00
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
Housing	Metal
Mounting Details	Wallmount
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-85% non-condensing
BTUs	19.8 BTU/Hr
COMMUNICATIONS	
Signal Range (ft.)	328



Powering Business Worldwide

TRIPP LITE
SERIES

Signal Range (m)	100
EDID Compatible	Yes
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
Latency	2-3 seconds
USB Extension Support	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	N202-Series Cat6 Patch Cable
STANDARDS & COMPLIANCE	
External Power Supply Certifications	BSMI; CB; CCC; CE; FCC; GS; PSE; RCM; TUV; UL; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.