

## 36V Extended Battery Module (EBM) for SU1000XLCD SmartOnline UPS Systems, Tower

MODEL NUMBER: BP36V



Provides extended runtime for compatible UPS systems in education, healthcare, military, government and other IT applications in small or mid-size networks.

### Features

#### Backup Battery Module Gives Your Compatible UPS System Extended Runtime

The valve-regulated lead-acid (VRLA) BP36V offers extended battery runtime when used in conjunction with SU1000XLCD SmartOnline® UPS systems. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

## Specifications

OVERVIEW	
UPC Code	037332279736
INPUT	
Input Phase	Single-Phase
Input Cord Details	15.7 in. connector cord
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	36
UPS Connection	UPS specific DC connector
PHYSICAL	
Primary Form Factor	Tower

### Highlights

- Connects to select expandable SmartOnline UPS systems to add critical runtime
- Includes heavy-gauge battery cabling with high-current 36V DC connectors
- Daisy-chain connector supports additional battery packs for even longer runtime

### System Requirements

Compatible only with 2023 redesign SU1000XLCD UPS systems

### Package Includes

- 36V Extended Battery Module
- External battery cable
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

Rack Height	0U
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	14.85 x 11.66 x 22.45
Shipping Weight (lbs.)	46.10
Shipping Weight (kg)	20.91
Unit Dimensions (hwd / in.)	9.930 x 6.300 x 15.240
Unit Weight (lbs.)	41.89
Unit Weight (kg)	19.00
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> Service Part Number: TL9SW5Y-3000BCParts, electronics and batteries coverageNext business day shippingTechnical support <b>5-YEAR ON-SITE PLAN (US ONLY)</b> Service Part Number: TLWEBN75XX-7000BCOnsite parts and labor coverage for 5 yearsParts, electronics and batteries coverage24x7 onsite labor coverage, next-day responseNext-day shippingTechnical support

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.