

Locking Caster Kit for Rolling TV/Monitor Carts - Heavy Duty, Swivel, 4 in. Diameter, 4 Casters

MODEL NUMBER: DMCCASTER



Replaces the existing smaller casters on Tripp Lite rolling TV/monitor carts with stronger, longer-lasting 4 in. steel casters.

Features

Modify Your Rolling TV/Monitor Cart for More Reliable Mobility from Room to Room This heavy-duty caster set lets you roll your rolling TV/monitor cart from one room to another, so you can safely, quickly and conveniently deliver your message directly to your audience. The DMCCASTER includes four swiveling casters, made from durable steel and measuring four inches in diameter. Each caster is specially designed for smooth rolling of heavy loads, even through doorways and across carpeting. A wrench is included for removing the stock casters from your rolling cart and installing these upgrades.

Highlights

- 4 heavy-duty casters roll smoothly across level floors and through doorways
- Ideal for easy movement from carpet to tile, wood, concrete or almost any surface
- Lock tight to keep the rolling cart securely in position while at rest
- Recommended for symmetrical ride across classrooms, offices, trade shows and lobbies

Applications

Upgrade your Tripp Lite rolling TV/monitor cart with sturdier metal casters designed for smooth, reliable movement

System Requirements

DMCS3770L, DMCS3270XP, DMCS60100XX and other compatible rolling TV/monitor carts

Package Includes

- (4) Swivel casters, 4 in.
- Wrench
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332249159
Accessory Type	Rolling Caster Kit
Accessory Class	Display Mount Accessories
PHYSICAL	
Color	Silver
Material of Construction	Steel
Unit Dimensions (hwd / in.)	5.310 x 1.260 x 3.940
Unit Weight (lbs.)	10
Unit Weight (kg)	4.54
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.