

Swivel/Tilt Wall Mount for 17" to 42" TVs and Monitors, 180° Swivel, -15° to +15° Tilt, -3° to +3° Screen Adjustment

MODEL NUMBER: DWM1742S



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM1742S Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 17 to 42 inches.

The full-motion swivel arm can be independently adjusted for angle and height to give you maximum flexibility in positioning your display to fit your environment and comfort level. An 180° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with soft rubber-feel finish supports up to 44 lbs (19.9 kgs). Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm and 200 x 200 mm.

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 17 to 42 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants Full-motion swivel arm adjusts independently for angle and height Mounting hardware included

Convenient One-Touch Adjustment 180° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability provides comfortable viewing from multiple angles

Durable Metal Construction Supports up to 44 lbs (19.9 kgs) Soft rubber-feel finish Fully assembled for immediate installation Display cables attach to mount to reduce clutter

VESA Compliance Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm and 200 x 200 mm

Highlights

- Fits most flat-panel displays from 17 to 42 in.
- One-touch adjustment for comfortable viewing
- 180° swivel, -15° to +15° tilt and -3° to +3° screen adjustment
- Supports up to 44 lbs (19.9 kgs)

Package Includes

- DWM1742S Swivel/Tilt Wall Mount for 17" to 42" TVs and Monitors
- (4) M4 x 14 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) D5 washers
- (4) D8 washers
- (8) Small spacers
- (3) Anchor bolts
- (3) Concrete anchors
- Wrench
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332183569
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black; Silver
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x200; 200x100; 200x200
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -3/+3 Level Adjustment
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Maximum Screen Size (in.)	42
Maximum Screen Size (cm)	106.68
Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20
Min/Max Arm Extension (in.)	2.16 min to 22.85 max
Min/Max Arm Extension (cm)	5.49 min to 58.04 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	3.60 x 19.60 x 15.70
Shipping Dimensions (hwd / cm)	9.14 x 49.78 x 39.88
Shipping Weight (lbs.)	10.40
Shipping Weight (kg)	4.72
Unit Dimensions (hwd / in.)	7.480 x 22.870 x 9.050
Unit Dimensions (hwd / cm)	19 x 58.1 x 23
Unit Weight (lbs.)	10.51
Unit Weight (kg)	4.77
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.