


Heavy-Duty Tilt Wall Mount for 32" to 80" Curved or Flat-Screen Displays

MODEL NUMBER: DWT3280X



Mounts a television or monitor on the wall in your classroom, conference room, restaurant, lobby or home theater.

Features

Mounts Your TV or Monitor on the Wall for a Perfect Viewing Angle

Recommended for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this low-profile TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most curved- and flat-screen displays from 32 to 80 inches and up to 165 pounds (75 kilograms).

Tilt Feature Lets You Adjust the Viewing Angle to Your Specifications

You can adjust the horizontal angle of your display from -8° to +0°. This will minimize glare on the screen and allow you to customize the angle for comfortable viewing.

Durable All-Metal Construction Provides Convenient Cable Access

The DWT3280X is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Its open frame design with smooth edges enables easy access to cabling. Horizontal mounting rails adjust to compensate for off-center wall studs. Removing and replacing the display is fast and simple using the automatic spring locks with quick-release cords.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 150 x 100, 150 x 150, 200 x 100, 200 x 200, 200 x 400, 300 x 200, 300 x 300, 350 x 350, 400 x 200, 400 x 300, 400 x 400, 600 x 200, 600 x 300 and 600 x 400.

Mounting hardware is included.

Specifications

OVERVIEW	
UPC Code	037332275783
Device Compatibility	Monitor/HDTV

Highlights

- Accepts most popular curved and flat-screen displays from 32 to 80 in. up to 165 lb. (75 kg.)
- Automatic spring locks with quick-release cords ensure quick and easy display removal
- Adjustable horizontal mounting rails help compensate for off-center wall studs
- Open-back architecture enables easy access to cables and power cords
- Conforms to current VESA standards to ensure compatibility with your display

System Requirements

Supports VESA mounting hole patterns 150 x 100, 150 x 150, 200 x 100, 200 x 200, 200 x 400, 300 x 200, 300 x 300, 350 x 350, 400 x 200, 400 x 300, 400 x 400, 600 x 200, 600 x 300 and 600 x 400

Package Includes

- DWT3280X Heavy-Duty Tilt Wall Mount
- Mounting hardware
- Owner's manual

PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	150x100; 150x150; 200x100; 200x200; 200x400; 300x200; 300x300; 350x350; 400x200; 400x300; 400x400; 600x200; 600x300; 600x400
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-8/+0 Tilt
Distance from Wall (in.)	1.46
Distance from Wall (cm)	4
Distance from Wall (mm)	37
Minimum Screen Size (in.)	32
Minimum Screen Size (cm)	81.28
Maximum Screen Size (in.)	80
Maximum Screen Size (cm)	203.20
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Number of Displays	1
Shipping Dimensions (hwd / in.)	18.60 x 9.30 x 1.90
Shipping Dimensions (hwd / cm)	47.24 x 23.62 x 4.83
Shipping Weight (lbs.)	3.96
Shipping Weight (kg)	1.80
Unit Dimensions (hwd / in.)	16.500 x 25.200 x 1.500
Unit Dimensions (hwd / cm)	16.5 x 25.2 x 1.50
Unit Weight (lbs.)	3.25
Unit Weight (kg)	1.47
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	REACH; RoHS3



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

5-year limited warranty

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks
are the property of their respective owners.