

FireWire IEEE 1394 Cable (6pin/6pin M/M) 6 ft. (1.83 m)

MODEL NUMBER: F005-006



Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity
- Retail packaging

System Requirements

- Two Firewire IEEE 1394 devices each with 6 Pin Female connectors.

Package Includes

- 6 Foot External Firewire (IEEE 1394) Cable 6 Pin to 6 Pin.

Features

- All Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps

Specifications

OVERVIEW	
UPC Code	037332011961
Technology	FireWire
CONNECTIONS	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	6 PIN (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.23
Shipping Weight (kg)	0.10
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.