

Isobar 10-Outlet Home/Business Theater Surge Protector, 8 ft. Cord with Right-Angle Plug, 3840 Joules, LEDs, Metal Housing

MODEL NUMBER: HT10DBS



Premium protection for A/V home or business theater components, including HDTVs and stereo receivers, against dangerous power surges, spikes and line noise. Recommended for medium-to-large home and business theater installations.

Features

Network-Grade 3840-Joule Surge Protection for Your Home or Business Theater Protects your A/V components against even the strongest surges and spikes Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression Exceeds IEEE 587 Category A and B surge suppression specifications

10 Outlets Accept Wide Range of Electronic Devices 10 NEMA 5-15R AC outlets accept most home theater equipment 4 widely spaced outlets accommodate bulky transformers without blocking other outlets Included safety covers block accidental contact with unused outlets Color-coded labels make it easy to coordinate outlets with equipment cords

Isolated Filter Banks Provide Extra Protection Outlets arranged in 2 exclusive isolated filter banks to limit noise interaction among connected equipment Block disruptive EMI/RFI line noise up to 60 dB that can cause equipment damage or data loss Combine large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

Protects Coaxial/Telephone/Modem/Ethernet Connections From Surges 3-line 2.2 GHz gold coaxial protection 1-line telephone/modem protection 1-line high-speed 10/100 Mbps Ethernet protection

Premium Safety Features Lighted on/off switch provides one-touch control over connected equipment Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Diagnostic LEDs confirm power, protection and line fault status at a glance Conforms to current UL 1449 3rd Edition safety standards

Fits Effortlessly Into Your Setup 8 ft. (2.4 m) AC power cord reaches nearby outlets Space-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wall Keyhole slots on bottom panel provide convenient wall or desk mounting options Metal housing designed for long life

Backed by Ultimate Lifetime Insurance \$500,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Highlights

- 10 NEMA 5-15R outlets in exclusive isolated filter banks
- Network-grade 3840-joule surge protection rating
- Coaxial/telephone/modem/Ethernet surge protection
- 12A resettable circuit breaker prevents dangerous overloads
- 8 ft. power cord with space-saving right-angle NEMA 5-15P plug

Package Includes

- HT10DBS Isobar 10-Outlet Home/Business Theater Surge Protector, Metal Housing
- RJ11 telephone cable, 6 ft.
- RG59 coaxial cable, 6 ft.
- RJ45 Cat5 Ethernet cable, 6 ft.
- (4) Outlet safety covers
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332121745
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(6) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm line power, protection and ground status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Up to 60 dB
Isolated Filter Banks	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	Yes
PHYSICAL	
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal tabs = 355.09 mm; Distance between vertical tabs = 58.17 mm
Outlets Measurement (Center to Center)	Distance between horizontal standard outlets = 39.45mm; Distance between horizontal transformer outlets = 53mm; Distance between vertical outlets = 38.76mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	16.50 x 3.10 x 9.20
Shipping Dimensions (hwd / cm)	41.91 x 7.87 x 23.37
Shipping Weight (lbs.)	4.60
Shipping Weight (kg)	2.09
Unit Dimensions (hwd / in.)	2.500 x 14.500 x 3.500
Unit Dimensions (hwd / cm)	36.2 x 2 x 5.7
Unit Weight (lbs.)	3.5
Unit Weight (kg)	1.59
COMMUNICATIONS	
Network Compatibility	100 Mbps (Fast Ethernet)
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); UL 1449; UL 497A
Product Compliance	FCC Part 68; RoHS



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$500,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.