

## Safe-IT 1-Port Single-Gang Keystone Wall Plate, Antibacterial, Ivory Matte, TAA

MODEL NUMBER: N042AB-001-IVM



Clean, simple faceplate with keystone jack port mounts to a wall for terminating premise audio/video, voice or data applications.

### Features

#### 1-Port Wall Plate Connects Your In-Wall Audio/Video, Voice or Data Cable Lines

This single-gang wall plate provides a clean, simple method for terminating your premise wiring applications, including home theater (audio/video), VoIP phones (voice) and Ethernet (data). Any type of keystone jack, including those used in HDMI, Cat5/6, USB and DisplayPort installations, snaps easily into the cutout for quick cable connection.

#### Provides Extra Protection Against Certain Bacteria

The wall plate is constructed using an antibacterial material that is effective in inhibiting *Escherichia coli* (E. coli) and *Staphylococcus aureus* (staph) and tested to ISO 22196:2011 standards. This added protection makes this cover plate an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This durable faceplate with an ivory matte finish blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

#### TAA-Compliant for GSA Schedule Purchases

The N042AB-001-IVM is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Made with antibacterial material proven effective in inhibiting E. coli and staph
- Compatible with all keystone jack types, including HDMI, Cat5/6, USB and DisplayPort
- High-impact plastic construction designed to blend in with your home/office decor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- N042AB-001-IVM 1-Port Single-Gang Antibacterial Keystone Wall Plate, Ivory Matte
- (2) Mounting screws

## Specifications

| OVERVIEW       |                                                                        |
|----------------|------------------------------------------------------------------------|
| UPC Code       | 037332269096                                                           |
| Accessory Type | Wall Plate                                                             |
| Technology     | Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed) |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                            |
|--------------------------------------|--------------------------------------------|
| Country/Region                       | Global                                     |
| <b>CONNECTIONS</b>                   |                                            |
| Number of Ports                      | 1                                          |
| Side A - Connector 1                 | KEYSTONE JACK CUTOUT                       |
| <b>PHYSICAL</b>                      |                                            |
| Color                                | Ivory                                      |
| Material of Construction             | ABS (ABS-764)                              |
| Total Number of Ports                | 1                                          |
| Unit Dimensions (hwd / in.)          | 4.840 x 3.110 x 0.440                      |
| Finish                               | Matte                                      |
| <b>ENVIRONMENTAL</b>                 |                                            |
| Operating Temperature Range          | 14° to 140°F (-10° to 60°C)                |
| Storage Temperature Range            | -40° to 154°F (-40° to 68°C)               |
| Operating Humidity Range             | 10% to 90% RH, (Non-Condensing)            |
| Storage Humidity Range               | 10% to 90% RH, (Non-Condensing)            |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                            |
| Antibacterial                        | Yes                                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                            |
| Product Certifications               | CSA (Canada); UL 94; UL Listed; cUL Listed |
| Product Compliance                   | RoHS; REACH; Trade Agreements Act (TAA)    |
| <b>WARRANTY &amp; SUPPORT</b>        |                                            |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty                  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.