

Toolless Shielded Cat6a Keystone Jack, PoE/PoE+ Compliant, Shuttered - Silver, TAA

MODEL NUMBER: **N238-001-SH-TFA**



Terminate your shielded Cat6a wall jack without using a punchdown tool. Ideal for wallplates, patch panels and surface-mount boxes.

Description

Strengthen your high-speed network with the N238-001-SH-TFA Toolless Shielded Cat6a Keystone Jack. Terminate your Cat6a wall jack without using a punchdown tool. Just lace the conductors into the stuffer cap, press the 110 connector, and lock the jack into place. Use in wallplates, patch panels and surface-mount boxes. Power over Ethernet Plus (PoE+) compliant. RJ45 port is compatible with all shielded Cat6a cables, and toolless punchdown connection is compatible with 22-24 AWG solid wire cabling. The N238-001-SH-TFA's protective housing is fully shielded to reduce EMI/RFI interference that can damage or degrade data.

Features

Strengthens Your High-Speed Network Ideal for wallplates, patch panels and surface-mount boxes. Lets you terminate your Cat6a wall jack without using a punchdown tool. Toolless punchdown connection compatible with 22-24 AWG Solid Wire cabling. RJ45 port compatible with all Shielded Cat6a cables. Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion.

Superior Construction for Superior Performance Fully shielded housing cuts down on EMI/RFI interference that can damage or degrade data. Features a shutter / dust cap that protects from dust and contaminants when not in use. UL-listed. Meets all EIA/TIA Cat6a requirements.

TAA-Compliant Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchasing.

Specifications

OVERVIEW	
UPC Code	037332189967
Product Type	RJ45 Keystone Jack
Technology	Cat6a
CONNECTIONS	

Highlights

- Easy to terminate—no punchdown tool required
- Protective shielded housing reduces EMI/RFI interference
- Features a shutter / dust cap that protects from dust and contaminants when not in use
- Keystone design for use with wallplates, patch panels and surface mount boxes
- Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion
- Meets all EIA/TIA Cat6a requirements

Package Includes

- N238-001-SH-TFA Toolless Shielded Cat6a Keystone Jack, PoE+ Compliant, Silver



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
PHYSICAL	
Color	Silver
Connector Color	Silver; White
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	5.000 x 4.000 x 0.500
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.