

Cat6a 24-Port High-Density Shielded Patch Panel - Dual IDC, 568A/B, RJ45 Ethernet, 0.5U Rack-Mount

MODEL NUMBER: N252A-024-HUSHK



Shielded 24-port patch panel manages and organizes Cat6a input/output cable connections in your high-density Gigabit Ethernet network.

Features

Shielded 24-Port Patch Panel Manages and Organizes High-Density Cat6a Network

Cabling Organize your high-density Cat6a application without taking up too much valuable rack space. This shielded patch panel offers 24 fully shielded RJ45 ports with color-coded dual IDC slots that are terminated using either a proper Krone or 110 punchdown tool. Both the front and rear connectors are clearly numbered and labeled (for custom naming) to help you identify individual cable runs. The patch panel supports T568A and T568B wiring standards and is fully rated for 10 Gbps Ethernet data transfer speeds in your network application.

Condenses 24 Ports into Just 0.5U of Space in Your 19 in. Enclosure or Open Frame Rack The high-density UL-approved patch panel supports mounting in only a half-U in EIA-standard 19-inch racks, freeing up valuable rack space for other equipment. Included cable ties, grounding wire and a built-in strain relief bar help organize your connections, cut down on cord clutter, take stress off the connectors and maintain stable performance.

Specifications

OVERVIEW	
UPC Code	037332248183
Product Type	Rackmount
Technology	Cat6a
CONNECTIONS	
Number of Ports	24
Side A - Connector 1	RJ45 (FEMALE)

Highlights

- 24 RJ45 ports numbered, labeled and color-coded for easy cable identification
- Rated for 10 Gbps speeds for managing Cat6a cable in high-density Ethernet applications
- Dual IDC terminations allow use of either Krone or 110 punchdown impact tool
- Built-in strain relief bar takes stress off connectors and cuts cable clutter
- Mounts easily into 0.5U of space in your EIA-standard 19 in. rack for immediate use

Applications

- Connect computers, routers, switches, wireless access points, security cameras, sensors and other high-speed devices in a 10G network configuration

Package Includes

- N252A-024-HUSHK Cat6a 24-Port Patch Panel, 0.5U
- (4) Cable ties
- (4) Screws
- Grounding wire
- Installation guide



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	KRONE IDC
PHYSICAL	
Rack Height	0.5U
Panel Style	Punchdown
COMMUNICATIONS	
Network Speed Details	Rated for 10GbE
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.