

Industrial Gigabit SFP Transceiver - 1000Base-SX, Multimode, LC Duplex, DDM, -40° to 85°C, 550 m (1,804 ft.), TAA

MODEL NUMBER: N286I-1P25GSXD



Industrial transceiver module links a Gigabit Ethernet network fiber cable to the SFP port on a switch, firewall or other network device.

Features

Industrial-Grade SFP Transceiver Module Connects Fiber Cabling to Your Network Device

N286I-1P25GSXD provides 1000Base-SX throughput over multimode fiber cable up to 550 meters (1,804 feet) at 850 nm. It complies with IEEE 802.3z 1000Base-SX standards, supports Digital Diagnostic Monitoring (DDM) and transmits bi-directional data at speeds up to 1.25 Gbps. Connect the transceiver to any standard SFP slot on an industrial switch or fiber converter, such as NGI-Series Industrial Gigabit Ethernet Switches.

Built to Last in Harsh Industrial Environments

The N286I-1P25GSXD adds 10/100/1000 Mbps Gigabit Ethernet connectivity to your industrial application, such as factory automation, rail and intelligent transportation systems (ITSs), marine, oil and gas, mining and other environments with wide temperature ranges. The high-strength housing withstands vibration, shock and free fall. It can also operate in extreme temperatures ranging from -40 to 85 degrees Celsius (-40 to 185 degrees Fahrenheit).

Hot-Pluggable for Installation Without Network Interruption

This transceiver module is fully hot-pluggable, so you can install it without a potentially costly network shutdown or device reboot. Just plug the SFP end of the transceiver into your network device. The other end has an LC duplex connector to link with high-speed fiber cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

Specifications

OVERVIEW	
UPC Code	037332268341
Product Type	Industrial Gigabit SFP Transceiver
Brand Compatibility	TRENDnet

Highlights

- Ideal for harsh environments, including factories, oil and gas, mines and rail systems
- Provides 1000Base-SX throughput up to 550 m via multimode fiber cabling
- Hot-swappable interface lets you install and uninstall without shutting down
- Industrial-grade transceiver supports operating temperature range of -40° to 85°C
- Supports bi-directional Gigabit Ethernet data transfer rates up to 1.25 Gbps

System Requirements

Works with standard SFP slots found on industrial switches and fiber converters, such as NGI Series

Package Includes

N286I-1P25GSXD Industrial Gigabit SFP Transceiver



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	SFP (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
PHYSICAL	
Unit Dimensions (hwd / in.)	0.430 x 0.550 x 2.640
Unit Weight (lbs.)	0.0359
Unit Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	-40° to 185°F (-40° to 85°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 95%
Operating Temperature	-40 to 185 F (-40 to 85 C)
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
Wavelength	850nm
Transmission Distance	550 m
FEATURES & SPECIFICATIONS	
Data Transfer Rate	1 Gbps
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; IEEE 802.3z 1000Base-SX/LX; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.