

16-Port Fiber Patch Panel, 1U (LC/LC), Multimode or Singlemode

MODEL NUMBER: **N490-016-LCLC**



Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125 or 50/125, Singlemode 9/125
- 16 ports in 1U of rackspace

Package Includes

- 16 Port LC/LC Duplex Multimode / Singlemode Fiber Optic Patch Panel

Description

This 16-port 1U rack-mount LC/LC Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-through duplex multimode connectors are mounted on a 16-gauge, cold-rolled, black powder-coated steel panel. Use with 62.5/125 or 50/125 Multimode and 9/125 Singlemode fiber Ethernet cables. Panel measures 19 inches wide by 1.75 inches high.

Features

- 16 ports LC/LC
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 fiber patch cables, and 9/125 Singlemode
- Available in ST/ST, SC/SC, LC/LC

Specifications

OVERVIEW	
UPC Code	037332135360
Product Type	Feed-Through
Technology	Multimode
CONNECTIONS	
Number of Ports	16
Side A - Connector 1	LC DUPLEX (FEMALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	2.80 x 3.00 x 19.60
Shipping Dimensions (hwd / cm)	7.11 x 7.62 x 49.78
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
Panel Style	Pass-Through
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.