

## DC Power Supply for N785-CH12 Media Converter Chassis, 75W, TAA

MODEL NUMBER: N785-CH75W-DC



75W DC power supply provides primary or redundant power to your media converter installation.

### Features

#### Powers Your N785-CH12 12-Port Media Converter Chassis

This 75-watt DC power supply works with the N785-CH12 media converter chassis to provide primary or redundant power. The N785-CH12 comes with a pre-installed AC power supply, but you can swap it out for the N785-CH75W-DC if you prefer DC power. This DC power supply can be used with any DC power source up to 48V 3A. A second DC power supply is also recommended to provide redundant power that helps prevent unwanted and expensive downtime. **Note:** Only one type of power supply should be used with the N785-CH12. Do not mix DC and AC power supplies.

## Specifications

OVERVIEW	
UPC Code	037332267078
Accessory Type	Power Supply
Accessory Class	Networking Accessories
INPUT	
AC Power Adapter Plug(s)	NEMA 5-15P North America
AC Power Adapter Input Specs (V / Hz / A)	48V / 3A
AC Power Adapter Output Specs (V / A)	12V / 6.5A
AC Power Adapter Cord Length (ft.)	6
AC Power Adapter Cord Length (m)	1.83
POWER	

### Highlights

- Supplies DC power to a media converter installation using N785-CH12
- Multiple power supplies provide primary and redundant power to prevent downtime

### System Requirements

N785-CH12 Media Converter Chassis

### Package Includes

N785-CH75W-DC 75W DC Power Supply



Powering Business Worldwide

TRIPP LITE  
SERIES

Power Source Type	AC Adapter
<b>PHYSICAL</b>	
Power Cord Color	Black
Unit Dimensions (hwd / in.)	5.240 x 2.320 x 9.060
Unit Dimensions (hwd / cm)	13.3 x 5.9 x 23.0
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 90%
Storage Humidity Range	5% to 95%
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
Auto MDIX Support	No
<b>STANDARDS &amp; COMPLIANCE</b>	
External Power Supply Certifications	CE; FCC; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.