

## Power Cord Adapter, C8 to C13 - 10A, 125V, Black

MODEL NUMBER: P003-000



### Highlights

- Recommended for powering laptops, video game systems and other C7 peripherals
- Converts a C7 connector into a C13 connector to match available C14 inlet

### Applications

- Connect a laptop, video game console or other device with a C7 plug to a C14 inlet

### Package Includes

- P003-000 IEC C8 to IEC C13 Power Cord Adapter, Black

C8 to C13 adapter allows you to connect your laptop or other device with a C7 plug to a UPS with a C14 power inlet.

### Features

**IEC C8 to IEC C13 Adapter Connects Laptops, Video Game Consoles and Other Equipment** This UL-listed power cord adapter is designed for home/office setups. It converts a C7 plug into a C13 connector and is ideal for a device's built-in power cord that doesn't match the available outlet. You can use this adapter to connect a laptop, video game system, radio, printer or other device with a C7 plug to a surge protector or UPS system with C14 power inlets.

## Specifications

| OVERVIEW                    |                                                     |
|-----------------------------|-----------------------------------------------------|
| UPC Code                    | 037332217967                                        |
| Device Compatibility        | Laptop; Video Game System; Radio; Printer; UPS; PDU |
| Country/Region              | North America                                       |
| INPUT                       |                                                     |
| Maximum Input Amps          | 10                                                  |
| Voltage Compatibility (VAC) | 125                                                 |
| CONNECTIONS                 |                                                     |
| Side A - Connector 1        | IEC-320-C8                                          |
| Side B - Connector 1        | IEC-320-C13                                         |
| PHYSICAL                    |                                                     |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Plug Color                           | Black                               |
| Cable Length (ft.)                   | 0                                   |
| Cable Length (m)                     | 0.00                                |
| Shipping Dimensions (hwd / in.)      | 5.00 x 3.98 x 0.50                  |
| Shipping Dimensions (hwd / cm)       | 12.70 x 10.11 x 1.27                |
| Shipping Weight (lbs.)               | 0.07                                |
| Shipping Weight (kg)                 | 0.03                                |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | 14° to 140°F (-10° to 60°C)         |
| Storage Temperature Range            | 14° to 140°F (-10° to 60°C)         |
| Operating Humidity Range             | 30% to 80% RH                       |
| Storage Humidity Range               | 30% to 80% RH                       |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| Antibacterial                        | No                                  |
| Angled Plug                          | No                                  |
| High Voltage                         | No                                  |
| Locking Plug                         | No                                  |
| Coiled Power Cord                    | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Certifications               | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                   | RoHS; REACH                         |
| <b>WARRANTY &amp; SUPPORT</b>        |                                     |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty           |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.