

Computer Power Cord Adapter, NEMA 5-15P to C13 - 15A, 125V, Black

MODEL NUMBER: P006-000



5-15R to C13 adapter allows you to connect your PC, printer or monitor into a surge protector or UPS with a NEMA 5-15R outlet.

Features

5-15P to C13 Adapter Connects PCs, Printers, Monitors and Other Equipment This UL-listed power cord adapter is designed for home/office desktop computer setups. It converts a C14 plug into a NEMA 5-15P connector and is ideal for a device's built-in power cord that doesn't match an available outlet. You can use this adapter to connect a computer, monitor, printer, scanner or other device with a C14 connector to a NEMA 5-15R wall outlet, surge protector or UPS system.

Specifications

OVERVIEW	
UPC Code	037332217974
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
PHYSICAL	

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- Converts a C14 connector into a NEMA 5-15P connector to match available outlet

Applications

- Connect devices like computers, printers and monitors to a NEMA 5-15R outlet near your workstation

Package Includes

- NEMA 5-15P to C13 Power Cord Adapter, Black



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Wire Gauge (OD - mm ²)	N/A
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	5.00 x 3.98 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.11 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	30% to 80% RH
Storage Humidity Range	30% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.