

## Y Splitter Power Cable, NEMA 5-15P to 2x C13 - 10A, 125V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: **P006-006-2**



Power cord splitter allows two devices with C14 inlets to share one AC power input cord and one NEMA 5-15R outlet.

### Features

**Y-Style Power Cord Splitter Connects 2 Devices with C14 Inlets to One AC Outlet** This computer power cord splitter allows two devices with C14 power inlets to share one AC input cord and one NEMA 5-15R outlet. The AC power splitter features a NEMA 5-15P plug for connecting to an AC power source and two C13 ends for connecting to devices. By connecting two devices to one outlet, the 6-ft. (1.83 m) power cord splitter frees up space in a PDU or surge protector and allows welcome flexibility in placing equipment with respect to the power outlet.

**Dual IEC Cable Powers a Wide Variety of Essential Electronics** With this PC power splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this dual IEC power cable is compatible with power and extension cords.

## Specifications

OVERVIEW	
UPC Code	037332148971
Device Compatibility	Computer; Monitor/HDTV; Printer; Scanner; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P

### Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing Y splitter power cable
- NEMA 5-15P plug connects to AC power; C13 plugs connect to devices' C14 inlets

### Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 6-ft. (1.83 m) away in your home office, work space or dorm room
- Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

### Package Includes

- P006-006-2 Y Splitter Power Cable, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	(2) IEC-320-C13
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 1.27
Shipping Weight (lbs.)	0.77
Shipping Weight (kg)	0.35
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.