

Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 13A, 125V, 16 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P006-008-13A



Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 8-ft. (2.43 m) length allows you some flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332180544
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
PHYSICAL	

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 8-ft. (2.43 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing NEMA 5-15P to C13 extension cord

Applications

- Connect devices like computers, printers and monitors to a PDU up to 8-ft. (2.43 m) away in your workstation
- Extend an existing power connection up to 8-ft. (2.43 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P006-008-13A NEMA 5-15P to C13 Desktop Computer AC Power Cable, 8-ft. (2.43 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.5mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	8
Cable Length (m)	2.44
Shipping Dimensions (hwd / in.)	12.80 x 7.10 x 0.10
Shipping Dimensions (hwd / cm)	32.51 x 18.03 x 0.25
Shipping Weight (lbs.)	0.64
Shipping Weight (kg)	0.29
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.