

## Safe-IT Antibacterial Hospital-Grade Power Cord, 5-15P to C13 - Green Dot, 13A, 125V, 16 AWG, Black, 15 ft. (4.6 m)

MODEL NUMBER: P006AB-015-HG



Hospital-grade power cord with antibacterial properties connects your PC or other device with a C14 inlet to a grounded AC outlet.

### Features

#### Hospital-Grade Power Cable is a Safe Solution for Medical Facilities

This Safe-IT™ hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient care vicinities. The 15-foot (4.6-meter) length allows you great flexibility in placing equipment with respect to the power outlet.

#### Provides Extra Protection Against Certain Bacteria

The connectors and PVC jacket are constructed using an antibacterial material that is effective in inhibiting the growth of Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical environments, such as hospitals, laboratories and clinics, and anywhere else that needs extra protection against bacteria.

#### Designed and Tested to Strict Hospital-Grade Standards

This cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

### Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- Made with antibacterial material proven effective in inhibiting the growth of E. coli and staph
- 15 ft. length allows great flexibility in placing devices in relationship to AC outlet
- Tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49 standards

### Package Includes

P006AB-015-HG Antibacterial Hospital-Grade Power Cord, 5-15P to C13, Black, 15 ft. (4.6 m)

## Specifications

| OVERVIEW             |                                                                |
|----------------------|----------------------------------------------------------------|
| UPC Code             | 037332266286                                                   |
| Device Compatibility | Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU |
| Country/Region       | North America                                                  |
| INPUT                |                                                                |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Maximum Input Amps                   | 13                                  |
| Voltage Compatibility (VAC)          | 125                                 |
| <b>CONNECTIONS</b>                   |                                     |
| Side A - Connector 1                 | NEMA 5-15P                          |
| Side B - Connector 1                 | IEC-320-C13                         |
| <b>PHYSICAL</b>                      |                                     |
| Plug Color                           | Black                               |
| Cable Jacket Color                   | Black                               |
| Connector Color                      | Black                               |
| Cable Jacket Material                | PVC                                 |
| Cable Jacket Rating                  | FT2                                 |
| Power Cord Jacket Type               | SJT                                 |
| Cable Outer Diameter (OD)            | 8.25mm                              |
| Number of Conductors                 | 3                                   |
| Wire Gauge (AWG)                     | 16                                  |
| Wire Gauge (OD - mm <sup>2</sup> )   | 1.31                                |
| Cable Length (ft.)                   | 15                                  |
| Cable Length (m)                     | 4.57                                |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | -4° to 221°F (-20° to 105°C)        |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C)         |
| Operating Humidity Range             | 20% to 80% RH, Non-Condensing       |
| Storage Humidity Range               | 20% to 80% RH, Non-Condensing       |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| Antibacterial                        | Yes                                 |
| Angled Plug                          | No                                  |
| High Voltage                         | No                                  |
| Locking Plug                         | No                                  |
| Coiled Power Cord                    | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Certifications               | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                   | RoHS; REACH                         |

WARRANTY & SUPPORT

|                                        |                           |
|----------------------------------------|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |
|----------------------------------------|---------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.