


## Hospital-Grade Extension Cord, NEMA 5-15P to NEMA 5-15R - Green Dot, 13A, 125V, 16 AWG, 6 ft. (1.83 m), Gray

MODEL NUMBER: **P022-006-GY-HG**



Hospital-grade extension cord connects two devices with 5-15P-HG/5-15R-HG power connectors in a hospital or other medical facility.

### Features

**Hospital-Grade Extension Cord is a Safe Solution for Medical Facilities** This hospital-grade power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment within a healthcare facility. It features a NEMA 5-15R-HG end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Designed and Tested to Strict Hospital-Grade Standards** This cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This extension cord features a gray SJT jacket and fully molded gray ends. The color-coding allows easy, fast identification in a crowded surge protector and helps prevent the cable from becoming inadvertently disconnected.

### Specifications

OVERVIEW	
UPC Code	037332200105
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125

### Highlights

- Adds 6-ft. (1.83 m) to your existing power connection to provide flexibility in placing devices
- Medical power cord replaces or upgrades power cord provided by manufacturer
- 5-15P-HG plug connects to AC power; 5-15R-HG end connects to device's input cord
- Color-coded gray for fast, easy identification in a crowded PDU, UPS or surge protector

### Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 6-ft. (1.83 m) away in a hospital environment
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P022-006-GY-HG Hospital-Grade Extension Cord, 5-15P-HG to 5-15R-HG, 6-ft. (1.83 m), Gray



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	NEMA 5-15R
PHYSICAL	
Plug Color	Gray
Cable Jacket Color	Gray
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.31
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS



*Powering Business Worldwide*

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.