

Extension Cord Y Splitter, Right-Angle NEMA 5-15P to 2x NEMA 5-15R - Heavy Duty, 15A, 120V, 14 AWG, 1 ft. (0.3 m), Black

MODEL NUMBER: P024-001-15D-2



Extension cord splitter allows two devices with NEMA 5-15P plugs to share one AC power input cord and one NEMA 5-15R outlet.

Features

Y-Style Power Cord Splitter Connects 2 Devices with 5-15P Plugs to One AC Outlet

This extension cable splitter allows two devices with NEMA 5-15P plugs to share one AC input cord and one NEMA 5-15R outlet. The AC power splitter features a right-angle 5-15P plug for connecting to an AC power source and two 5-15R ends for connecting to devices' power cords. By connecting two devices to one power outlet, the splitter frees up space in a PDU or surge protector, reduces cable clutter and allows welcome flexibility in placing equipment with respect to the outlet.

Heavy-Duty 14 AWG Cable Powers a Wide Variety of Essential Electronics

With this extension cord splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, scanners, printers, instrument amplifiers and other equipment in your home office, work space or dorm room. Ideal for areas where AC outlets are limited, such as rack cabinets, this extension cord Y splitter is compatible with most brands of power cords.

Right-Angle Plug Makes Connecting in Tight Spaces Easier

The space-saving right-angle NEMA 5-15P plug is easy to connect to an outlet located in a confined area, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and helps prevent the cable from bending awkwardly.

Specifications

OVERVIEW	
UPC Code	037332268549
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other home/office devices
- Right-angle 5-15P plug allows easier connection in confined or hard-to-reach spaces
- Adds 1 ft. to your existing power connection to add flexibility in placing devices
- NEMA 5-15P plug connects to AC power; 5-15R ends connect to devices' cords

Package Includes

P024-001-15D-2 Extension Cord Y Splitter, 1 ft. (0.3 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Input Amps	15
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P - RIGHT ANGLE
Side B - Connector 1	(2) NEMA 5-15R
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	1
Cable Length (m)	0.30
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH, Non-Condensing
Storage Humidity Range	20% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	Yes
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks
are the property of their respective owners.