

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P024-006-13A



6 ft. extension cord with 5-15P and 5-15R connectors connects bulky power transformers without blocking adjacent outlets on your PDU.

Features

6-ft. (1.83 m) Extension Cord Connects PCs, Printers, Monitors and Other Equipment This cord is recommended for home/office desktop computer applications, home theater setups or other applications where multiple devices are plugged into a surge protector, PDU or UPS system. It allows you to connect bulky power adapters to a NEMA 5-15R outlet without blocking adjacent outlets. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 6-ft. (1.83 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P024-006-13A 6-Ft Extension Cord, NEMA 5-15P to NEMA 5-15R, Black

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332180605 |
| Product Type | PDU Extension Power Cord |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 13 |
| Voltage Compatibility (VAC) | 125 |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA 5-15P |
| Side B - Connector 1 | NEMA 5-15R |
| Connector Style | Straight |



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|------------------------------------|-----------------------------|
| Color | Black |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Connector Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | FT2 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 9mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 16 |
| Wire Gauge (OD - mm ²) | 1.31 |
| Power Cord Color | Black |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 10.00 x 7.10 x 0.10 |
| Shipping Dimensions (hwd / cm) | 25.40 x 18.03 x 0.25 |
| Shipping Weight (lbs.) | 0.53 |
| Shipping Weight (kg) | 0.24 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 20% to 80% RH |
| Storage Humidity Range | 20% to 80% RH |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | No |
| Locking Plug | No |
| Coiled Power Cord | No |
| Locking Power Cord | No |
| Locking | No |
| STANDARDS & COMPLIANCE | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Product Certifications | cUL Listed; UL Listed |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.