

## PDU Power Cords, C19 to P-Lock C20 - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.8 m), Black, 6 Pack

MODEL NUMBER: **P036-E06-6**



Connect blade servers or network switches to a PDU with a P-Lock C19 or C39 power connector and extend your existing power connection by 6 ft.

### Features

#### C20-to-C19 Power Cables for Network Devices That Require a Heavy-Gauge Connection

These power extension cords feature 12 AWG wire suitable for high power connections, making them a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The P036-E06-6 can be used to connect servers, routers, network switches or blade server enclosures to a UPS system or PDU. The six-foot (1.8-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU in a crowded rack enclosure. Six PDU power cables are included, an ideal pack for large-scale equipment rollouts.

#### Forms a Special Locking Connection with a P-Lock Outlet

The P-Lock C20 connector forms a secure connection with a PDU with a P-Lock outlet, including Eaton G4 and newer PDUs with C39 outlets. The P-Lock connection helps reduce costly downtime caused by accidental cable disconnections in a crowded rack or PDU space. The P036-E06-6 lets you replace non-locking C19/C20 cables or upgrade an entire PDU application by pairing with an Eaton PDU or other PDU with P-Lock outlets.

## Specifications

OVERVIEW	
UPC Code	037332292667
Product Type	PDU Power Cord
Device Compatibility	Computer; Monitor/HDTV; PDU; Printer; Server; Tablet; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	20

### Highlights

- Recommended for powering servers, routers and other high-output network devices
- P-Lock C20 connector eliminates accidental cable disconnections in a crowded PDU
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- 6 ft. length allows flexibility in mounting devices within a rack while avoiding cable clutter
- 6 black PDU power cables included, ideal for large-scale equipment rollouts

### Package Includes

(6) PDU Power Cords, C19 to P-Lock C20, 6 ft. (1.8 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Voltage Compatibility (VAC)	250
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11.1mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	18.11 x 14.17 x 1.00
Shipping Weight (lbs.)	6.55
Shipping Weight (kg)	2.97
Unit Dimensions (hwd / in.)	11.000 x 7.000 x 0.500
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	23° to 158°F (-5° to 70°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Relative Humidity	35 TO 85% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
P-Lock Power Cord	Yes
Locking Power Cord	Yes



*Powering Business Worldwide*

TRIPP LITE  
SERIES

**STANDARDS & COMPLIANCE**

Product Certifications	cUL Listed; UL Listed
------------------------	-----------------------

**WARRANTY & SUPPORT**

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.