




Powering Business Worldwide

TRIPP LITE
SERIES

PDU Power Cords, C19 to P-Lock C20 - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.8 m), White, 6 Pack

MODEL NUMBER: **P036-E06-AWH-6**



Connect blade servers or network switches to a PDU with a P-Lock C19 or C39 power connector and extend your existing power connection by 6 ft.

Features

C20-to-C19 Power Cables for Network Devices That Require a Heavy-Gauge Connection

These power extension cords feature 12 AWG wire suitable for high power connections, making them a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The P036-E06-AWH-6 can be used to connect servers, routers, network switches or blade server enclosures to a UPS system or PDU. The six-foot (1.8-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU in a crowded rack enclosure. Six PDU power cables are included, an ideal pack for large-scale equipment rollouts.

Forms a Special Locking Connection with a P-Lock Outlet

The P-Lock C20 connector forms a secure connection with a PDU with a P-Lock outlet, including Eaton G4 and newer PDUs with C39 outlets. The P-Lock connection helps reduce costly downtime caused by accidental cable disconnections in a crowded rack or PDU space. The P036-E06-AWH-6 lets you replace non-locking C19/C20 cables or upgrade an entire PDU application by pairing with an Eaton PDU or other PDU with P-Lock outlets.

White Jackets Help Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cables have a white PVC jacket with fully molded white ends, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cables from becoming accidentally disconnected.

Highlights

- Recommended for powering servers, routers and other high-output network devices
- P-Lock C20 connector eliminates accidental cable disconnections in a crowded PDU
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- White cable jacket allows quick identification of devices in a crowded rack enclosure
- 6 PDU power cables included, ideal for large-scale equipment rollouts

Package Includes

(6) PDU Power Cords, C19 to P-Lock C20, 6 ft. (1.8 m), White

Specifications

OVERVIEW	
UPC Code	037332292698
Product Type	PDU Power Cord
Device Compatibility	Computer; Monitor/HDTV; PDU; Printer; Server; Tablet; UPS



Powering Business Worldwide

TRIPP LITE
SERIES

Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19
PHYSICAL	
Plug Color	White
Cable Jacket Color	White
Connector Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11.1mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	18.11 x 14.17 x 1.00
Shipping Weight (kg)	2.97
Unit Dimensions (hwd / in.)	11.000 x 7.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	23° to 158°F (-5° to 70°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Relative Humidity	35 TO 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.