

Mini DVI to HDMI Cable Adapter, Video Converter for Macbooks and iMacs, (M/F)

MODEL NUMBER: P138-000-HDMI



Highlights

- Connect a HDMI Display to Apple Intel iMac, MacBook, and 12in PowerBook G4 mini-DVI Port
- 8 inch overall length

System Requirements

- Apple Intel iMac, MacBook, and 12in PowerBook G4

Package Includes

- 8inch mini-DVI to HDMI Adapter

Description

This mini-DVI to HDMI Digital Female Video Adapter Cable allows you to connect a HDMI display to the mini-DVI port found on some Apple computer models. Supports Single-Link digital transmission with resolutions up to 1920 x 1200 at 60 Hz.

Features

- Connect a HDMI Display to Apple Intel iMac, MacBook, and 12in PowerBook G4 mini-DVI Port
- 8 inch overall length
- 1920x1200@60Hz resolution

Specifications

OVERVIEW	
UPC Code	037332152145
Product Type	Video Adapter
Device Compatibility	Computer; Laptop
Technology	DVI; HDMI
CONNECTIONS	
Side A - Connector 1	MINI-DVI (MALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	White
Cable Jacket Color	White



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (ft.)	0.7
Cable Length (m)	0.21
Cable Length (in.)	8
Cable Length (cm)	20.32
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Unit Weight (lbs.)	0.3000
Unit Weight (kg)	0.14
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.