

Keyspan Mini DisplayPort to DisplayPort Adapter, 4K 60 Hz, Black (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P139-06N-DP4K6B



Mini DisplayPort adapter connects your 4K DisplayPort display to the mDP or Thunderbolt 1 or 2 port on your laptop, smartphone or tablet.

Features

Mini DisplayPort Adapter Sends mDP Audio/Video to a DisplayPort Monitor

Transmits Crystal-Clear 4K Video and Digital Audio

Boldly Constructed for Superior Performance

Ready to Use Right Out of the Package

Lifetime Warranty and Environmentally Responsible Design

Highlights

- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Saves you the expense of buying a new mDP monitor
- Foil and braid shielding protects against line noise that can distort or destroy data
- Gold-plated contacts guarantee a clear transmission free of interference
- Easy installation with plug-and-play operation—no software required

Applications

- Transmit 4K video and digital audio from your computer's Mini DisplayPort or Thunderbolt 1 or 2 output to your existing DisplayPort monitor or other display
- Carry it with your Mini DisplayPort laptop for showing video at trade shows, presentations or lectures
- Display digital signage in your office, brick-and-mortar store, school or church

System Requirements

- Source device with Mini DisplayPort or Thunderbolt 1 or 2 output
- Display device with DisplayPort input

Package Includes

- P139-06N-DP4K6B Mini DisplayPort to DisplayPort Adapter—4K x 2K @ 60 Hz, Keyspan, Black, 6 in.

Specifications

OVERVIEW	
UPC Code	037332210692
Product Type	Video Adapter
Technology	DisplayPort



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.