

3.5 mm Mini Stereo to RCA Audio Y Splitter Adapter Cable (F/2xM), 6 in. (15.2 cm)

MODEL NUMBER: **P316-06N**



Highlights

- Converts a 3.5mm Stereo plug to 2 x RCA Male plugs or 2 x RCA Male plugs to a 3.5mm stereo plug
- Shielded, flexible cable

Package Includes

- 6-inch 3.5mm Female to 2 x RCA Male adapter

Convert a 3.5mm Stereo plug to RCA Stereo plugs or RCA stereo plugs to a 3.5mm stereo plug

Features

- 6-inch 3.5mm Female to 2 x RCA Male
- Molded ends for a Lifetime of use
- Shielded cable protects from outside noise interference
- Color coded Red / White RCA's for accurate connections

Specifications

| OVERVIEW | |
|--------------------------------|----------------|
| UPC Code | 037332183996 |
| Product Type | Passive Cable |
| Technology | Stereo Audio |
| Cable Type | Passive |
| CONNECTIONS | |
| Side A - Connector 1 | 3.5MM (FEMALE) |
| Side B - Connector 1 | (2) RCA (MALE) |
| Latching or Gripping Connector | No |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|---------------------------|
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Length (ft.) | 0.5 |
| Cable Length (m) | 0.15 |
| Cable Length (in.) | 6 |
| Cable Length (cm) | 15.24 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Weight (lbs.) | 0.08 |
| Shipping Weight (kg) | 0.04 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.