

## RJ45 to DB9F Cisco Serial Console Port Rollover Cable, 6 ft. (1.83 m)

MODEL NUMBER: **P430-006**



### Highlights

- 6-ft. (1.83 m) DB9F to RJ45 console rollover cable
- Equivalent to Cisco AIR-CONCAB1200 console port cable (72-3383-01)
- P430-006 is a passive cable - no chipset or driver required

### System Requirements

- Computer with DB9M Serial port
- Cisco networking hardware with RJ45 console port

### Package Includes

- 6-ft. (1.83 m) RJ45 to DB9F Cisco Serial Console Port Rollover Cable

### Features

- 6ft DB9F to RJ45 Console Rollover Cable
- Equivalent to Cisco AIR-CONCAB1200, 72-3382-01
- Connects a computer DB9M serial port to a RJ45 Cisco Console port

## Specifications

| OVERVIEW                        |                      |
|---------------------------------|----------------------|
| UPC Code                        | 037332188311         |
| Technology                      | Serial               |
| CONNECTIONS                     |                      |
| Side A - Connector 1            | DB9 (FEMALE)         |
| Side B - Connector 1            | RJ45 (MALE)          |
| PHYSICAL                        |                      |
| Color                           | Blue                 |
| Cable Jacket Color              | Blue                 |
| Cable Length (ft.)              | 6                    |
| Cable Length (m)                | 1.83                 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50   |
| Shipping Dimensions (hwd / cm)  | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.)          | 0.14                 |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Weight (kg)                | 0.06                      |
| Unit Dimensions (hwd / in.)         | 9.000 x 7.000 x 0.500     |
| STANDARDS & COMPLIANCE              |                           |
| Product Compliance                  | REACH; RoHS               |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.