

VGA High-Resolution RGB Coaxial Cable (HD15 M/F), 50 ft. (15.24 m)

MODEL NUMBER: **P500-050**



Extend the high-resolution connection between your VGA-enabled computer and monitor up to 50 ft. with no ghosting. Recommended for easy access to VGA ports that are hidden or hard to reach.

Features

Extends Connection Between VGA-Enabled Computer and Monitor Up to 50 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

OVERVIEW	
UPC Code	037332125293
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input

Package Includes

- P500-050 VGA Coax High-Resolution Monitor Extension Cable (M/F), 50 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 1.00
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 2.54
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC/EN 60068-2-64; IEC/EN 60068; IEC/EN 62040
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.