

Low-Profile VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 6 ft. (1.83 m)

MODEL NUMBER: P502-006-SM



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 6 ft. apart with no ghosting.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 6 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded HD15 male connectors and gold-plated contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Special Slim Design

- More than 40% smaller in diameter than standard VGA cable
- Increases airflow in tight spaces
- Increased flexibility for installing around corners

Specifications

OVERVIEW	
UPC Code	037332163271
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive
CONNECTIONS	

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated contacts for maximum conductivity
- Over 40% slimmer than standard VGA cables

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

- P502-006-SM Low-Profile VGA Coaxial High-Resolution Monitor Cable (M/M), 6 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	HD15 (MALE) - LOW PROFILE
Side B - Connector 1	HD15 (MALE) - LOW PROFILE
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	0.10 x 5.10 x 8.70
Shipping Dimensions (hwd / cm)	0.25 x 12.95 x 22.10
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.