

VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 25 ft. (7.62 m)

MODEL NUMBER: **P502-025**



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 25 ft. apart with no ghosting.

Description

The P502-025 VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 25-ft. (7.62 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 25-ft. (7.62 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

OVERVIEW	
UPC Code	037332125286
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

- P502-025 VGA Coaxial High-Resolution Monitor Cable (M/M), 25-ft. (7.62 m)



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.62
Cable Length (in.)	300
Shipping Dimensions (hwd / in.)	2.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	5.08 x 25.40 x 1.27
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC/EN 60068-2-64; IEC/EN 60068; IEC/EN 62040
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.