

VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M), 50 ft. (15.24 m)

MODEL NUMBER: P504-050



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm stereo plugs

Package Includes

- SVGA/VGA Monitor Cable (HD15M to HD15M w/Built-in 3.5mm Audio connectors) - 50 ft.

Features

- Extend both video and audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality
- HD15 male to HD15 male and 3.5mm to 3.5mm molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

Specifications

OVERVIEW	
UPC Code	037332139238
Product Type	Passive Cable
Technology	Coax; VGA/SVGA; Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 1.00
Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 2.54
Shipping Weight (lbs.)	2.65
Shipping Weight (kg)	1.20
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.