

VGA Monitor Extension Cable, 640x480 (HD15 M/F), 10 ft. (3.05 m)

MODEL NUMBER: **P510-010**



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

System Requirements

- Monitor with HD15 cable and resolutions up to 640x480.

Package Includes

- 10-ft. VGA Monitor Extension HD15F to HD15M Gold Connectors

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

Specifications

OVERVIEW	
UPC Code	037332012340
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.