

High Resolution VGA Monitor Y Splitter Cable (HD15 M to 2x HD15 F), 6 ft. (1.83 m)

MODEL NUMBER: **P516-006-HR**



Highlights

- Splits the SXGA/UXGA signal providing simultaneous display of the same image on two monitors
- HD15 Male splits to 2 HD15 Female, 6-ft

System Requirements

A computer with a VGA port, and two monitors with VGA ports

Package Includes

- 6-ft. SXGA/UXGA Hi-Res Splitter Cable, HD15M to 2 x HD1F

Features

- HD15 Male to 2 x HD15 Female w/Hex Nuts
- RGB cable construction supports resolutions up to 1600 x 1200
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the same image from one PC
- Inexpensive solution for presentations

Specifications

OVERVIEW	
UPC Code	037332187789
Product Type	Splitter
Technology	VGA/SVGA
Host Connector	HD15 (MALE)
Cable Type	Passive
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Latching or Gripping Connector	No
Input x Output	1 x 2
Daisy-chainable / Cascadable	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
FEATURES & SPECIFICATIONS	
MST Support	No
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.