

## DVI Y Splitter Cable, Digital Monitors (DVI-D M to 2x F), 1 ft. (0.31 m)

MODEL NUMBER: P564-001



### Features

- DVI-D Male to 2 x DVI-D Female, 1 ft.
- Inexpensive solution for presentations
- Supports video resolutions up to 1920 x 1080
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the same image from one PC
- The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected

### Highlights

- Splits the digital (DVI) signal providing simultaneous display of the same image on two DVI monitors
- DVI-D male splits to two (2) DVI-D females
- Supports video resolutions up to 1920 x 1080

### System Requirements

- DVI-D or DVI-I Female PC Card Connector, and DVI Enabled Monitors
- The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected

### Package Includes

- DVI-D Male to (2) DVI-D Female Cable - 1 ft.

## Specifications

OVERVIEW	
UPC Code	037332138798
Product Type	Splitter
Technology	DVI
Host Connector	DVI-D DUAL LINK (MALE)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	(2) DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Latching or Gripping Connector	No
Input x Output	1 x 2



Powering Business Worldwide

TRIPP LITE  
SERIES

Daisy-chainable / Cascadable	No
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
<b>FEATURES &amp; SPECIFICATIONS</b>	
MST Support	No
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.