

# DisplayPort 1.2 to HDMI Active Adapter Cable (M/M), 4K 60 Hz, Gripping HDMI Plug, HDCP 2.2, 12 ft. (3.7 m), TAA

MODEL NUMBER: **P582-012-HD-V2A**



HDCP 2.2-compliant cable connects the DisplayPort output on your PC or Mac to a 4K-enabled HDMI monitor, projector or television.

## Features

**Send UHD DisplayPort 1.2a Signals to a 4K HDMI Display** Connects DisplayPort PC or Mac to a 4K-enabled HDMI monitor, projector or HDTV Recommended for displaying video on a large monitor or digital sign DisplayPort and high-grip HDMI male connectors No separate power adapter required

**Vibrant Video Quality** Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160), as specified in HDMI 2.0 Supports HDCP 2.2, audio and EDID Active adapter compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output Recommended for graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

**Superior Materials for Superior Performance** Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss Special high-grip HDMI plug prevents accidental disconnections Integral strain relief provides cable and connectors with flexibility and reduces stress

## Highlights

- Supports video resolutions up to 4K @ 60 Hz (3840 x 2160)
- Compliant with latest HDCP 2.2 standards and EDID
- No separate power adapter required
- High-grip HDMI plug prevents accidental disconnections

## Package Includes

- P582-012-HD-V2A DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 12 ft.

## Specifications

| OVERVIEW                       |                         |
|--------------------------------|-------------------------|
| UPC Code                       | 037332200754            |
| Product Type                   | Active Cable            |
| Technology                     | HDMI; DisplayPort       |
| Cable Type                     | Active                  |
| VIDEO                          |                         |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 60Hz |



Powering Business Worldwide

TRIPP LITE  
SERIES

| CONNECTIONS                         |                                                                             |
|-------------------------------------|-----------------------------------------------------------------------------|
| Side A - Connector 1                | DISPLAYPORT (MALE)                                                          |
| Side B - Connector 1                | HDMI (MALE)                                                                 |
| PHYSICAL                            |                                                                             |
| Color                               | Black                                                                       |
| Cable Jacket Color                  | Black                                                                       |
| Cable Jacket Material               | PVC                                                                         |
| Cable Jacket Rating                 | VW-1                                                                        |
| Cable Length (ft.)                  | 12                                                                          |
| Cable Length (m)                    | 3.66                                                                        |
| Cable Length (in.)                  | 144                                                                         |
| Shipping Dimensions (hwd / in.)     | 0.50 x 10.00 x 12.00                                                        |
| Shipping Dimensions (hwd / cm)      | 1.27 x 25.40 x 30.48                                                        |
| Shipping Weight (lbs.)              | 0.60                                                                        |
| Shipping Weight (kg)                | 0.27                                                                        |
| STANDARDS & COMPLIANCE              |                                                                             |
| Product Compliance                  | CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE; Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                                                                             |
| Product Warranty Period (Worldwide) | 3-year limited warranty                                                     |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.