

USB Cable Kit for KVM Switch B006-VU4-R, 6 ft. (1.83 m)

MODEL NUMBER: **P758-006**



Highlights

- Required to connect a USB computer to the B006-VU4-R KVM switch
- KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable
- Computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable

System Requirements

- A USB computer
- A USB KVM switch (model # B006-VU4-R).

Package Includes

- 6-ft. USB Cable Kit for the B006-VU4-R KVM Switch

Features

- Required to connect a USB computer to a B006-VU4-R KVM switch
- KVM switch side of the cable kit consists of a USB Type B Male cable and a SVGA (HD15) Female monitor cable
- Computer side of the cable kit consists of a USB Type A Male cable and a SVGA (HD15) Male monitor cable
- Molded ends with easy-grip textured overmold
- Supports any VGA/SVGA monitor
- Constructed of mini-coax (RGB) and paired video wire
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Hi-Resolution cable

Specifications

OVERVIEW	
UPC Code	037332014986
Accessory Type	Cable Kit
Technology	VGA/SVGA
Accessory Class	KVM Switch Accessories
CONNECTIONS	
KVM Switch Side 1	HD15 (Female)
KVM Switch Side 2	USB B (Male)
Computer Side 1	HD15 (Male)



Powering Business Worldwide

TRIPP LITE
SERIES

Computer Side 2	USB A (Male)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.