

VGA to DisplayPort and USB-A Adapter Cable Kit for B020-U and B022-U KVM, 6 ft. (1.8 m)

MODEL NUMBER: P778-006-DP



Connects a DisplayPort server to the VGA port on your Tripp Lite NetDirector® KVM switch.

Features

Connect Your Computer's DisplayPort and USB Ports to a KVM Switch

This convenient cable kit saves you money by combining necessary cables into one bunch. For use with B020-U and B022-U KVM switches, the P778-006-DP features male DisplayPort and USB-A connectors for your server or computer and a male HD15 connector for the KVM. The DisplayPort 1.1-compliant cable supports HD resolutions up to 1920 x 1080 (1080p) at 60 Hz with 36-bit Deep Color. The USB 2.0 cable supports 480 Mbps speeds. The bus-powered cable kit requires no software or external power adapter. A sliding switch on the back of the housing lets you decide between USB power mode or USB + DP power mode with LEDs indicating which mode you have chosen.

Highlights

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- LEDs indicate at a glance which power mode the cable kit is using
- Supports USB 2.0 speeds up to 480 Mbps for reliable data transfers
- Plug and play with no software or external power supply required
- Compatible only with select B020-U and B022-U Series KVM switches

Applications

Transfer data and video between your KVM switch and a connected server or computer

System Requirements

B022-U08, B022-U08-IP, B022-U16-IP, B020-U08-19-IP, B020-U16-19-IP, B020-U08-19-K or B020-U16-19-K KVM switch

Package Includes

P778-006-DP VGA to DisplayPort and USB Adapter Cable Kit, 6 ft. (1.8 m)

Specifications

OVERVIEW	
UPC Code	037332263353
Accessory Type	Cable Kit
Technology	DVI; USB
Accessory Class	KVM Switch Accessories
VIDEO	
Max Supported Video Resolution	1920 x 1080 60 Hz
Max Supported Color Depth	36-bit Deep Color
HDR Support	No
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	DISPLAYPORT (MALE); USB A (MALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green - USB & DP Power; Orange - USB Power Only
PHYSICAL	
Cable Jacket Color	Black
Connector Color	Black; Green
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	USB: 3.5MM; DisplayPort: 6.0MM
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	2.40 x 4.60 x 6.30
Shipping Weight (kg)	0.32
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	0 TO 80% RH, Non-Condensing
Storage Humidity Range	0 TO 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Displayport Specification	1.1
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.