

USB/PS2 Combo Cable for NetDirector KVM Switches B020-U08/U16 and KVM B022-U16, 15 ft. (4.57 m)

MODEL NUMBER: **P778-015**



Description

The P778-015 KVM cable kit is designed to connect a USB or PS2 computer to NetDirector® KVM Switches B020-U08-19-K and B020-U16-19-K. This premium all-in-1 cable provides superior performance and cable management. It consists of a USB and PS/2 keyboard/mouse cable and a monitor cable bonded into a single unit. This low-profile cable is incredibly flexible, making cable management a breeze. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Connects a USB or PS2 Computer to NetDirector B020-U08-19-K and B020-U16-19-K KVM Switches
- Makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a modified HD18 Male cable
- Computer side of the cable kit consists of a HD15 Male cable, USB A Male cable, and 2 x PS/2 Male cables
- Molded, color-coded connectors

Specifications

OVERVIEW	
UPC Code	037332155498
Accessory Type	Combo Cable
Technology	PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories
CONNECTIONS	

Highlights

- Connects a USB or PS2 Computer to NetDirector B020-U08-19-K and B020-U16-19-K KVM Switches
- Makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a modified HD18 Male cable
- Computer side of the cable kit consists of a HD15 Male cable, USB A Male cable, and 2 x PS/2 Male cables
- Molded, color-coded connectors

System Requirements

- This cable can only be used with the following KVM Switch models: B020-U08-19-K and B020-U16-19-K.
- Servers or computers with PS/2 or USB Mouse/Keyboard connections

Package Includes

15-ft. (4.57 m) P778-006 All-in-one KVM Cable Kit



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	USB A (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	0.75
Shipping Weight (kg)	0.34
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.