

Daisy Chain Cable for NetController KVM Switches B040-Series and B042-Series, 6 ft. (1.83 m)

MODEL NUMBER: **P781-006**



Description

Molded HD15 Male/Female Daisy-Chain cable, specifically wired for B040- and B042-Series KVM switches. Double shielded and fully molded construction for optimum video transfer and long life.

Features

- Daisy Chain cable for B040 and B042 series KVM switches
- Fully molded construction, with double shielding
- HD15 Male/Female 6-ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332146496
Accessory Type	Daisy-Chain Cable
Accessory Class	KVM Switch Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	8.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	20.32 x 25.40 x 1.27

Highlights

- Molded HD15 Male/Female, 6-ft. (1.83 m)
- Double Shielded
- For Daisy Chaining B040 and B042 KVM switches

System Requirements

Use only with B040 and B042 series KVM switches, to daisy chain additional KVM switches.

Package Includes

6-ft. (1.83 m) HD15 Male/Female B040 / B042 KVM Daisy Chain Cable



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (lbs.)	0.47
Shipping Weight (kg)	0.21
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.