

HDMI/DVI/USB KVM Cable Kit, 10 ft. (3.05 m) - USB 2.0, 4K 60Hz

MODEL NUMBER: P782-010-DH



Connects your HDMI- or DVI-enabled computer to a Tripp Lite HDMI KVM switch up to 10 ft. away.

Description

The P782-010-DH HDMI/DVI/USB KVM Cable Kit connects your computer to an HDMI-enabled KVM switch. It includes a 10-foot (3.1-meter) USB A/B keyboard/mouse cable, a 10-foot HDMI monitor cable and an adapter for converting a DVI port to HDMI. Premium foil and braid shielding in the cables delivers reliable, error-free signal quality and protection from EMI/RFI interference. Integral strain relief ensures the cable and connectors last a long time. The adapter's molded gold-plated connectors and contacts ensure excellent conductivity.

Features

Connects Your Computer to a HDMI KVM SwitchIncludes 10 ft. USB A/B cable, 10-ft. (3.05 m) HDMI cable and DVI-to-HDMI adapterHDMI cable support crystal-clear video resolutions up to 4K x 2K (3840 x 2160) @60 Hz.USB A/B cable support data transfer speeds up to 480 Mbps.HDMI to DVI-D adapter support resolutions up to 1920 x 1080 @60 Hz.

First-Rate Construction for Superior Signal TransferPremium foil and braid shielding for EMI/RFI noise protectionMolded gold-plated connectors and contacts for optimal signal qualityIntegral strain relief for long lifeFlexible PVC jackets easy to install in tight spaces

Highlights

- Includes 10-ft. (3.05 m) USB A/B and HDMI cables
- Includes DVI-to-HDMI adapter
- Premium foil and braid shielding
- Integral strain relief
- Molded gold-plated connectors and contacts

System Requirements

- Computer with available USB port and available HDMI or DVI port
- HDMI KVM switch

Package Includes

- USB 2.0 cable (A/B M/M), 10-ft. (3.05 m)
- HDMI cable (M/M), 10-ft. (3.05 m)
- HDMI to DVI-D Dual Link adapter (F/M)

Specifications

OVERVIEW	
UPC Code	037332199898
Accessory Type	Cable Kit
Technology	DVI; HDMI
Accessory Class	KVM Switch Accessories
VIDEO	
Max Supported Video Resolution	HDMI: 3840 x 2160 @60Hz, DVI: 1920 x 1080 @60Hz



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK); HDMI (MALE); USB B (MALE)
Side B - Connector 1	HDMI (MALE); USB A (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	0.50 x 8.30 x 6.40
Shipping Dimensions (hwd / cm)	1.27 x 21.08 x 16.26
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.