

## DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M) + DP (M/M), 4K, 10 ft. (3.05 m), Black

MODEL NUMBER: P783-010-DPU



DisplayPort KVM cable kit includes cables with DP, USB and 3.5 mm plugs for connecting your computer to a Tripp Lite NIAP KVM.

### Features

**Cable Kit Specifically Designed for Select KVMs to Save You Time and Money** Recommended for the B002-DP2AC4 and B002-HD2AC4 NIAP KVM switches, this DisplayPort cable kit supports video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with true 4:4:4 chroma subsampling, as well as USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and costs.

**10-ft. (3.05 m) Cables Connect Your DisplayPort Computer to a NIAP KVM Switch with CAC** This KVM cable kit includes three 10-ft. (3.05 m) cables for connecting a computer with two monitors to a KVM switch with a Common Access Card (CAC) port. The P783-010 features DisplayPort, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The P580-010 is a DisplayPort cable with male connectors on each end. The U022-010 is a USB cable that connects to the KVM's CAC port for accessing smart cards, scanners and biometric readers, including fingerprint readers, to bolster security.

### Highlights

- 10-ft. (3.05 m) 3-in-1 DisplayPort, USB A/B and 3.5 mm cable connects KVM to your computer
- 10-ft. (3.05 m) DisplayPort cable included for connecting a second monitor to the KVM switch
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports true 4:4:4 chroma subsampling to meet latest color standards
- 10-ft. (3.05 m) USB A/B cable included for KVM's CAC port (smart cards, scanners, etc.)

### Applications

- Connect a headless computer with dual displays to a Tripp Lite KVM switch with CAC support
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter and save money by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 10 ft.

### System Requirements

- B002-DP2AC4 or B002-HD2AC4 NIAP KVM or other compatible KVM

### Package Includes

- P783-010 DisplayPort KVM cable kit, 3 in 1 (M/M), 10 ft.
- P580-010 DisplayPort monitor cable (M/M), 10 ft.
- U022-010 USB A/B cable (M/M), 10 ft.

## Specifications

OVERVIEW	
UPC Code	037332241627
Accessory Type	Cable Kit
Technology	DisplayPort



Powering Business Worldwide

TRIPP LITE  
SERIES

Accessory Class	KVM Switch Accessories
<b>VIDEO</b>	
Max Supported Video Resolution	3840 x 2160 (4K x 2K) @60Hz
<b>CONNECTIONS</b>	
Side A - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB A (MALE)
Side A - Connector 2	DISPLAYPORT (MALE)
Side A - Connector 3	USB A (MALE)
Side B - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB B (MALE)
Side B - Connector 2	DISPLAYPORT (MALE)
Side B - Connector 3	USB B (MALE)
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0-90% non-condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
Displayport Specification	1.2
HDCP Specification	2.2
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.