

eSATA, SATA-II External Signal Shielded Cable (7Pin/7Pin), 18-in. (45.72 cm)

MODEL NUMBER: **P950-18I**



Highlights

- Connect your high-speed eSATA device to a eSATA controller
- Support data transfer rates of up to 6Gbps
- Cable is double-shielded to protect against EMI/RFI

System Requirements

- eSATA Device
- eSATA Controller

Features

- Connect your high-speed eSATA device to an eSATA controller
- Support data transfer rates of up to 6Gbps
- 18" Cable is double-shielded to protect against EMI/RFI
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332130952
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	7 PIN ESATA (MALE)
Side B - Connector 1	7 PIN ESATA (MALE)
PHYSICAL	
Color	Blue
Cable Jacket Color	Blue
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Cable Length (in.)	18
Cable Length (cm)	45.72



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	0.25 x 6.00 x 6.00
Shipping Dimensions (hwd / cm)	0.64 x 15.24 x 15.24
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.