

# 1.5kW Single-Phase Local Metered PDU, 100-127V Outlets (13 5-15R), 5-15P, 100-127V Input, 15 ft. (4.57 m) Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH15-RA



## Highlights

- Local metered single phase 12A 100-127V PDU
- 1U horizontal rackmount, Digital current meter
- NEMA 5-15P input with 15-ft. (4.57 m) line cord
- 13 NEMA 5-15R outlets oriented with ground pin on the bottom (1 front / 12 rear)
- Reversible housing 4.5 in / 11.4cm depth

## Package Includes

- PDUMH15-RA Local Metered rackmount PDU
- Owner's manual with warranty information

## Features

- 15A single phase 100-127V Local Metered Power Distribution Unit / rack PDU (rPDU) (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA 5-15P 15A 100-120V input plug with 15-ft. (4.57 m) line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets oriented with the ground pin on the bottom (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

## Specifications

| OVERVIEW                       |                                   |
|--------------------------------|-----------------------------------|
| UPC Code                       | 037332183231                      |
| PDU Type                       | Local Metered                     |
| INPUT                          |                                   |
| Input Phase                    | Single-Phase                      |
| PDU Input Voltage              | 100; 120; 125; 127                |
| Recommended Electrical Service | Single-phase 15A 100-127V service |
| Maximum Input Amps             | 12                                |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                              |                                                                                     |
|----------------------------------------------|-------------------------------------------------------------------------------------|
| Maximum Input Amps Details                   | Agency de-rated to 12A continuous                                                   |
| PDU Plug Type                                | NEMA 5-15P                                                                          |
| Input Cord Length (ft.)                      | 15                                                                                  |
| Input Cord Length (m)                        | 4.57                                                                                |
| <b>OUTPUT</b>                                |                                                                                     |
| Output Capacity Details                      | 1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 12A total capacity; 12A max per outlet |
| Frequency Compatibility                      | 50 / 60 Hz                                                                          |
| Output Receptacles                           | (13) 5-15R                                                                          |
| Output Nominal Voltage                       | 100-127V                                                                            |
| Overload Protection                          | 15A circuit breaker                                                                 |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                                                                                     |
| Front Panel LCD Display                      | Digital display reports total PDU output current in amps                            |
| <b>SURGE / NOISE SUPPRESSION</b>             |                                                                                     |
| Automatic Shut-Off                           | No                                                                                  |
| <b>PHYSICAL</b>                              |                                                                                     |
| Material of Construction                     | Metal                                                                               |
| Rack Height                                  | 1U                                                                                  |
| Form Factors Supported                       | 1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation     |
| Minimum Required Rack Depth (cm)             | 17.27                                                                               |
| Minimum Required Rack Depth (inches)         | 6.8                                                                                 |
| PDU Form Factor                              | Horizontal (1U)                                                                     |
| Shipping Dimensions (hwd / in.)              | 2.25 x 20.50 x 10.00                                                                |
| Shipping Dimensions (hwd / cm)               | 5.72 x 52.07 x 25.40                                                                |
| Shipping Weight (lbs.)                       | 5.20                                                                                |
| Shipping Weight (kg)                         | 2.36                                                                                |
| Unit Dimensions (hwd / in.)                  | 1.750 x 17.300 x 3.750                                                              |
| Unit Dimensions (hwd / cm)                   | 4.45 x 44.45 x 9.5                                                                  |
| Unit Weight (lbs.)                           | 4.6                                                                                 |
| Unit Weight (kg)                             | 2.09                                                                                |
| <b>ENVIRONMENTAL</b>                         |                                                                                     |
| Operating Temperature Range                  | 32° to 104°F (0° to 40°C)                                                           |
| Storage Temperature Range                    | -22° to 122°F (-30° to 50°C)                                                        |

|                                     |                                            |
|-------------------------------------|--------------------------------------------|
| Relative Humidity                   | 5% to 95% non-condensing                   |
| Operating Elevation                 | 0-10000 ft. (0-3000 m)                     |
| FEATURES & SPECIFICATIONS           |                                            |
| Grounding                           | Rear grounding lug                         |
| STANDARDS & COMPLIANCE              |                                            |
| Product Certifications              | RETIE (Colombia); NOM (Mexico); UL 60950-1 |
| Product Compliance                  | RoHS                                       |
| WARRANTY & SUPPORT                  |                                            |
| Product Warranty Period (Worldwide) | 2-year limited warranty                    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.